



**CR Series**



PET 瓶口結晶機 PET Preform Neck Crystallizer



[www.keen-pro.com](http://www.keen-pro.com)



## 機台優勢 OUTSTANDING


### PET 瓶口結晶機

PET 結晶瓶，對生產者而言，耐撞擊不易變形，高度瓶壁結晶化，降低水與氧氣透過率，高充填溫度，有效防止細菌的污染，減少防腐劑添加；對消費者而言，可於第一時間檢視內容物的保存狀況，對食品安全性的信心提昇，增加購買的意願。

### PET Preform Neck Crystallizer

Crystallization of PET bottles, for producers, impact-resistant, not easily deformed, height wall crystallization, reduce water and oxygen transmission rate, high filling temperature effective to prevent bacterial contamination and to reduce the addition of preservatives; For consumers, the first time to view the state of conservation of the contents, and enhance confidence in food safety, increased willingness to buy.

## 機台結構 MACHINE STRUCTURE



## 機台規格表 CR Series Specification

| EM SERIES |                          | Unit           | CR6K  |
|-----------|--------------------------|----------------|-------|
| 理論產能      | Theoretical Production   | BPH            | 6000  |
| 瓶型規格      | Bottle Specification     |                |       |
| 最大瓶身直徑    | Max. Bottle Diameter     | mm             | 70    |
| 最大瓶身高度    | Max. Bottle Height       | mm             | 240   |
| 最大瓶胚高度    | Max. Preform Height      | mm             | 175   |
| 最大支撐環高度   | Max. Support-ring Height | mm             | 27    |
| 瓶胚牙口尺寸    | Preform Neck             | mm             | 15-32 |
| 機台規格      | Machine Specification    |                |       |
| 馬達功率      | Motor Power              | kw             | 3.5   |
| 加熱功率      | Heating Power            | kw             | 40    |
| 其他功率      | Other Power              | kw             | 0.5   |
| 機台安裝功率    | Machine Installed Power  | kw             | 44    |
| 機台尺寸      | Machine Dimension        | m <sup>2</sup> | 8     |
| 機台重量      | Machine Weight           | kg             | 2500  |



※實際產能依瓶胚規格、設計、品質而定。Actual production depends on customer's preform specification, design and quality.